

Han 3A-HSM angled-L-M20 bottom closed



| | |
|--------------------|---|
| Part number | 19 20 003 1252 |
| Specification | Han 3A-HSM angled-L-M20 bottom closed |
| HARTING eCatalogue | https://b2b.harting.com/19200031252 |

Identification

| | |
|-----------------------------|-------------------------|
| Category | Hoods/Housings |
| Series of hoods/housings | Han A® |
| Type of hood/housing | Surface mounted housing |
| Description of hood/housing | Bottom closed |

Version

| | |
|----------------------|---|
| Locking type | Single locking lever |
| Size | 3 A |
| Version | Top entry |
| Cable entry | 1x M20 |
| Field of application | Standard Hoods/housings for industrial applications |

Technical characteristics

| | |
|--|--|
| Limiting temperature | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP44 IP65 / IP67 with seal screw 09 20 000 9918 |

Material properties

| | |
|-------------------------|--|
| Material (hood/housing) | Zinc die-cast |
| Surface (hood/housing) | Powder-coated |
| Colour (hood/housing) | RAL 7037 (dust grey) |
| Material (locking) | Steel |
| Surface (locking) | Zinc plated |
| RoHS | compliant with exemption |
| RoHS exemptions | 6a: Lead as an alloying element in steel for machining purposes and in galvanised steel containing up to 0,35 % lead by weight |
| ELV status | compliant with exemption |
| China RoHS | 50 |



Pushing Performance

Material properties

| | |
|-----------------------------|----|
| REACH Annex XVII substances | No |
|-----------------------------|----|

| | |
|----------------------------|----|
| REACH ANNEX XIV substances | No |
|----------------------------|----|

| | |
|-----------------------|-----|
| REACH SVHC substances | Yes |
|-----------------------|-----|

| | |
|-----------------------|------|
| REACH SVHC substances | Lead |
|-----------------------|------|

Specifications and approvals

| | |
|-----------|--------|
| Approvals | DNV GL |
|-----------|--------|

Commercial data

| | |
|----------------|----|
| Packaging size | 10 |
|----------------|----|

| | |
|------------|---------|
| Net weight | 83.54 g |
|------------|---------|

| | |
|-------------------|---------|
| Country of origin | Germany |
|-------------------|---------|

| | |
|-----------------------|----------|
| Customs tariff number | 85389099 |
|-----------------------|----------|