

Han 16A-HSM-HC 1 Lever 2xM25



Part number	19 20 016 0291
Specification	Han 16A-HSM-HC 1 Lever 2xM25
HARTING eCatalogue	https://b2b.harting.com/19200160291

Identification

Category	Hoods/Housings
Series of hoods/housings Han A [®]	
Type of hood/housing	Surface mounted housing
Туре	Low construction

Version

Locking type	Single locking lever
Han-Easy Lock [®]	Yes
Size	16 A
Version	Side entry
Cable entry	2x M25
Field of application	Standard Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X
	12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (locking)	Polycarbonate Stainless steel
Colour (locking)	RAL 7037 (dust grey)
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant



Material properties

ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	176.2 g
Country of origin	Germany
Customs tariff number	85389099