

Han 32A-asg1-K-M25



Part number	19 20 032 0226
Specification	Han 32A-asg1-K-M25
HARTING eCatalogue	https://b2b.harting.com/19200320226

Identification

Category	Hoods/Housings
Series of hoods/housings	Han A®
Type of hood/housing	Surface mounted housing
Description of hood/housing	With thermo-plastic cover
Type	High construction

Version

Locking type	Double locking lever (on the hood)
Size	32 A
Version	Side entry
Cable entry	1x M25
Field of application	Standard Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant with exemption
RoHS exemptions	6a: Lead as an alloying element in steel for machining purposes and in galvanised steel containing up to 0,35 % lead by weight
ELV status	compliant with exemption
China RoHS	50



Pushing Performance

Material properties

REACH Annex XVII substances No

REACH ANNEX XIV substances No

REACH SVHC substances Yes

REACH SVHC substances Lead

Specifications and approvals

Approvals DNV GL

Commercial data

Packaging size 1

Net weight 464 g

Country of origin Germany

Customs tariff number 85389099