

Han B Base SM HC 1 Lever Metal Cover M25



Part number	19 30 006 7296
Specification	Han B Base SM HC 1 Lever Metal Cover M25
HARTING eCatalogue	https://b2b.harting.com/19300067296

Identification

Category	Hoods/Housings
Series of hoods/housingsHan®B	
Type of hood/housing	Surface mounted housing
Description of hood/ housing	With metal cover
Туре	High construction

Version

Locking type	Single locking lever
Han-Easy Lock [®]	Yes
Size	6 B
Version	Side entry
Cable entry	2x M25
Field of application	Standard hoods/housings for industrial connectors

Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
Material (locking)	Polycarbonate Stainless steel
Colour (locking)	RAL 7037 (dust grey)



Material properties

Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant with exemption
RoHS exemptions	6a: Lead as an alloying element in steel for machining purposes and in galvanised steel containing up to 0,35 $\%$ lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	360.4 g
Country of origin	Germany
Customs tariff number	85389099