

Han B Base Surface HC 1 Lever 2 x M25



| Part number | 19 30 016 0291 |
|--|---------------------------------------|
| Specification | Han B Base Surface HC 1 Lever 2 x M25 |
| HARTING eCatalogue | https://b2b.harting.com/19300160291 |
| | |
| Identification | |
| Category | Hoods/Housings |
| Series of hoods/housingsHan [®] B | |
| Type of hood/housing | Surface mounted housing |
| Туре | High construction |

Version

| Locking type | Single locking lever |
|----------------------------|---|
| Han-Easy Lock [®] | Yes |
| Size | 16 B |
| Version | Side entry |
| Cable entry | 2x M25 |
| Field of application | Standard hoods/housings for industrial connectors |

Technical characteristics

| Limiting temperature | -40 +125 °C |
|--|-------------|
| Degree of protection acc. to IEC 60529 | IP65 |
| Type rating acc. to UL 50 / UL 50E | 4 4X |
| | 12 |

Material properties

| Material (hood/housing) | Aluminium die-cast |
|--|----------------------------------|
| Surface (hood/housing) | Powder-coated |
| Colour (hood/housing) | RAL 7037 (dust grey) |
| Material (seal) | NBR |
| | |
| Material (locking) | Polycarbonate Stainless steel |
| Material (locking) Colour (locking) | |

Page 1 / 2 | Creation date 2018-09-07 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric GmbH & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



Material properties

| RoHS | compliant |
|-----------------------------|-----------|
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | No |

Specifications and approvals

| Approvals | DNV GL |
|-----------|-----------------------------------|
| UL / CSA | UL 1977 ECBT2.E235076 |
| | CSA-C22.2 No. 182.3 ECBT8.E235076 |

Commercial data

| Packaging size | 1 |
|-----------------------|----------|
| Net weight | 426.6 g |
| Country of origin | Germany |
| Customs tariff number | 85389099 |