

Han 3HPR angled hous. long version M25



Part number	19 40 003 0953
Specification	Han 3HPR angled hous. long version M25
HARTING eCatalogue	https://b2b.harting.com/19400030953

Identification

Category	Hoods/Housings
Series of hoods/housings	Han® HPR
Type of hood/housing	Surface mounted housing
Description of hood/housing	Long version Bottom closed Tapped blind hole for fixing screws

Version

Locking type	Screw locking
Size	3 A
Version	Top entry
Cable gland	1x M25
Field of application	Hoods/housings for harsh outdoor environments
Pack contents	With seal screw

Technical characteristics

Limiting temperature	-40 ... +125 °C
Tightening torque (screw locking)	2 Nm
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Chromated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR



Pushing Performance

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	219 g
Country of origin	Germany
Customs tariff number	85389099