

Han 3HPR Surface M. H. long, RoHS conf.



Part number	19 40 703 0951
Specification	Han 3HPR Surface M. H. long, RoHS conf.
HARTING eCatalogue	https://b2b.harting.com/19407030951

Identification

Category	Hoods/Housings
Series of hoods/housings	Han® HPR
Type of hood/housing	Surface mounted housing
Description of hood/housing	Angled
	Bottom closed
	Long version
	Bottom closed
	Feed through hole for fixing screws

Version

Locking type	Screw locking
Size	3 A
Version	Top entry
Cable gland	1x M25
Field of application	Hoods/housings for harsh outdoor environments
Pack contents	With seal screw

Technical characteristics

Limiting temperature	-40 ... +125 °C
Tightening torque (screw locking)	2 Nm
Degree of protection acc. to IEC 60529	IP65
	IP68
	IP69 / IPX9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)



Pushing Performance

Material properties

Material (seal)	NBR FPM
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	206.4 g
Country of origin	Germany
Customs tariff number	85389099