

Han-Eco Mod.24-HSM1-M40



Part number	19 41 024 0233
Specification	Han-Eco Mod.24-HSM1-M40
HARTING eCatalogue	https://b2b.harting.com/19410240233

Identification

Category	Hoods/Housings	
Series of hoods/housingsHan-Eco® Modular		
Type of hood/housing	Surface mounted housing	

Version

Locking type	Double locking lever
Size	24 B
Version	Side entry
Cable entry	1x M40

Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Polyamide Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Colour (seal)	RAL 9005 (jet black)
Material (locking)	Polyamide Fibre-glass reinforced
Colour (locking)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No



Material properties

REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	IEC 61984 EN 45545-2 R22: HL1, HL2, HL3 EN 45545-2 R23: HL1, HL2, HL3 EN 45545-2 R24: HL1, HL2, HL3
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	281 g
Country of origin	Germany
Customs tariff number	85389099