

## Han-Eco Mod.10 Outd.-HSM2-M32-glanded



|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| Part number        | 19 41 310 0272                                                                        |
| Specification      | Han-Eco Mod.10 Outd.-HSM2-M32-glanded                                                 |
| HARTING eCatalogue | <a href="https://b2b.harting.com/19413100272">https://b2b.harting.com/19413100272</a> |

### Identification

|                             |                             |
|-----------------------------|-----------------------------|
| Category                    | Hoods/Housings              |
| Series of hoods/housings    | Han-Eco® Modular            |
| Type of hood/housing        | Surface mounted housing     |
| Description of hood/housing | With integrated cable gland |

### Version

|              |                      |
|--------------|----------------------|
| Locking type | Double locking lever |
| Size         | 10 B                 |
| Version      | Side entry           |
| Cable entry  | 2x M32               |

### Technical characteristics

|                                        |                 |
|----------------------------------------|-----------------|
| Limiting temperature                   | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP65            |
| Clamping range                         | 13 ... 21 mm    |

### Material properties

|                                                            |                                     |
|------------------------------------------------------------|-------------------------------------|
| Material (hood/housing)                                    | Polyamide<br>Fibre-glass reinforced |
| Colour (hood/housing)                                      | RAL 9005 (jet black)                |
| Material (seal)                                            | FPM                                 |
| Colour (seal)                                              | RAL 7001 (silver-grey)              |
| Material (locking)                                         | Polyamide<br>Fibre-glass reinforced |
| Colour (locking)                                           | RAL 9005 (jet black)                |
| Material flammability class acc. to UL 94                  | V-0                                 |
| Material flammability class acc. to UL 94 (locking levers) | V-0                                 |
| RoHS                                                       | compliant                           |



Pushing Performance

## Material properties

|                             |           |
|-----------------------------|-----------|
| ELV status                  | compliant |
| China RoHS                  | e         |
| REACH Annex XVII substances | No        |
| REACH ANNEX XIV substances  | No        |
| REACH SVHC substances       | No        |

## Specifications and approvals

|                |                                   |
|----------------|-----------------------------------|
| Specifications | IEC 61984                         |
|                | EN 45545-2 R22: HL1, HL2, HL3     |
|                | EN 45545-2 R23: HL1, HL2, HL3     |
|                | EN 45545-2 R24: HL1, HL2, HL3     |
| UL / CSA       | UL 1977 ECBT2.E235076             |
|                | CSA-C22.2 No. 182.3 ECBT8.E235076 |

## Commercial data

|                       |          |
|-----------------------|----------|
| Packaging size        | 1        |
| Net weight            | 257 g    |
| Country of origin     | Germany  |
| Customs tariff number | 85389099 |