

Han A Hood Top Entry HC 4 Pegs PG 29



Part number	09 20 032 0421
Specification	Han A Hood Top Entry HC 4 Pegs PG 29
HARTING eCatalogue	https://b2b.harting.com/09200320421

Identification

Category	Hoods/Housings
Series of hoods/housings Han A [®]	
Type of hood/housing	Hoods
Туре	High construction

Version

Locking type	Double locking lever
Size	32 A
Version	Top entry
Cable entry	1x Pg 29
Field of application	Standard Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Material properties

REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	259 g
Country of origin	Germany
Customs tariff number	85389099