

Han A Hood Top Entry HC 2 Levers PG 21



Part number	09 20 032 0430
Specification	Han A Hood Top Entry HC 2 Levers PG 21
HARTING eCatalogue	https://b2b.harting.com/09200320430

Identification

Category	Hoods/Housings
Series of hoods/housings	Han A®
Type of hood/housing	Hoods
Type	High construction

Version

Locking type	Double locking lever (on the hood)
Han-Easy Lock®	Yes
Size	32 A
Version	Top entry
Cable entry	1x Pg 21
Field of application	Standard Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (locking)	Polycarbonate
	Stainless steel
Colour (locking)	RAL 7037 (dust grey)
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant with exemption



Pushing Performance

Material properties

RoHS exemptions 6c: Copper alloy containing up to 4 % lead by weight

ELV status compliant with exemption

China RoHS 50

REACH Annex XVII substances No

REACH ANNEX XIV substances No

REACH SVHC substances Yes

REACH SVHC substances Lead

Specifications and approvals

Approvals DNV GL

Commercial data

Packaging size 1

Net weight 297.2 g

Country of origin Germany

Customs tariff number 85389099