

Han A Hood Side Entry HC 4 Pegs PG 29



Part number	09 20 032 0521
Specification	Han A Hood Side Entry HC 4 Pegs PG 29
HARTING eCatalogue	https://b2b.harting.com/09200320521

Identification

Category	Hoods/Housings	
Series of hoods/housings Han A [®]		
Type of hood/housing	Hoods	
Туре	High construction	

Version

Locking type	Double locking lever
Size	32 A
Version	Side entry
Cable entry	1x Pg 29
Field of application	Standard Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Material properties

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076
UL / CSA	CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	240.7 g
Country of origin	Germany
Customs tariff number	85389099