

## Han B Hood Top Entry HC 2 Pegs PG 29



Part number	09 30 006 0443
Specification	Han B Hood Top Entry HC 2 Pegs PG 29
HARTING eCatalogue	<a href="https://b2b.harting.com/09300060443">https://b2b.harting.com/09300060443</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> B
Type of hood/housing	Hoods
Description of hood/housing	With adapter
Type	High construction

### Version

Locking type	Single locking lever
Size	6 B
Version	Top entry
Cable entry	1x Pg 29
Field of application	Standard hoods/housings for industrial connectors

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65 IP67 in combination with special bulkhead mounted housings
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50



Pushing Performance

## Material properties

REACH Annex XVII substances	No
-----------------------------	----

REACH ANNEX XIV substances	No
----------------------------	----

REACH SVHC substances	Yes
-----------------------	-----

REACH SVHC substances	Lead
-----------------------	------

## Specifications and approvals

Approvals	DNV GL
-----------	--------

UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076

## Commercial data

Packaging size	1
----------------	---

Net weight	160.7 g
------------	---------

Country of origin	Germany
-------------------	---------

Customs tariff number	85389099
-----------------------	----------