

# Han B Hood Side Entry HC 4 Reels Pg 36



Part number	09 30 032 0522
Specification	Han B Hood Side Entry HC 4 Reels Pg 36
HARTING eCatalogue	https://b2b.harting.com/09300320522

#### Identification

Category	Hoods/Housings
Series of hoods/housings Han® B	
Type of hood/housing	Hoods
Туре	High construction

#### Version

Locking type	Double locking lever
Size	32 B
Version	Side entry
Cable entry	1x Pg 36
Field of application	Standard hoods/housings for industrial connectors

## Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

#### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



## Material properties

|--|

## Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076

#### Commercial data

Packaging size	1
Net weight	555 g
Country of origin	Germany
Customs tariff number	85389099