

Han 10HPR Hood w/o Pg-Screw lock



Part number	09 40 010 0811
Specification	Han 10HPR Hood w/o Pg-Screw lock
HARTING eCatalogue	https://b2b.harting.com/09400100811

Identification

Category	Hoods/Housings	
Series of hoods/housingsHan® HPR		
Type of hood/housing	Hoods	

Version

Locking type	Screw locking
Size	10 B
Version	Without cable entry
Field of application	Hoods/housings for harsh outdoor environments

Technical characteristics

Limiting temperature	-40 +125 °C
Tightening torque (screw locking)	4 Nm
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Material properties

REACH SVHC substances No

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	505 g
Country of origin	Germany
Customs tariff number	85389099