

Han 24 HPR Hood Top Entry PG 29 Screw Lo



Part number	09 40 024 0413
Specification	Han 24 HPR Hood Top Entry PG 29 Screw Lo
HARTING eCatalogue	https://b2b.harting.com/09400240413

Identification

Identification	
Category	Hoods/Housings
Series of hoods/housingsHan® HPR	
Type of hood/housing	Hoods

Version

Locking type	Screw locking
Size	24 B
Version	Top entry
Cable gland	1x Pg 29
Field of application	Hoods/housings for harsh outdoor environments

Technical characteristics

Limiting temperature	-40 +125 °C
Tightening torque (screw locking)	4 Nm
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	е



Material properties

REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
	CSA-C22.2 NO. 102.3 ECB10.E233070

Commercial data

Packaging size	1
Net weight	62.84 g
Country of origin	Germany
Customs tariff number	85389099