

Han 24 HPR Hood Side Entry PG 36 Screw L



| Part number | 09 40 024 0514 |
|--------------------|---|
| Specification | Han 24 HPR Hood Side Entry PG 36 Screw L |
| HARTING eCatalogue | https://b2b.harting.com/09400240514 |

Identification

| Category | Hoods/Housings | |
|-----------------------------------|----------------|--|
| Series of hoods/housings Han® HPR | | |
| Type of hood/housing | g Hoods | |

Version

| Locking type | Screw locking |
|----------------------|---|
| Size | 24 B |
| Version | Side entry |
| Cable gland | 1x Pg 36 |
| Field of application | Hoods/housings for harsh outdoor environments |

Technical characteristics

| Limiting temperature | -40 +125 °C |
|--|--|
| Tightening torque (screw locking) | 4 Nm |
| Degree of protection acc. to IEC 60529 | IP65 IP68 IP69 / IPX9K acc. to ISO 20653 |
| Type rating acc. to UL 50 / UL 50E | 4 4X 12 |

Material properties

| Material (hood/housing) | Aluminium die-cast Corrosion resistant |
|-------------------------|--|
| Surface (hood/housing) | Powder-coated |
| Colour (hood/housing) | RAL 9005 (jet black) |
| Material (locking) | Stainless steel |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | е |



Material properties

| REACH Annex XVII substances | No |
|-----------------------------|----|
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | No |

Specifications and approvals

| Approvals | DNV GL |
|-----------|--|
| UL / CSA | UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076 |

Commercial data

| Packaging size | 1 |
|-----------------------|----------|
| Net weight | 629.6 g |
| Country of origin | Germany |
| Customs tariff number | 85389099 |