

Han 6 EMC/B-G



Part number	09 62 806 0801
Specification	Han 6 EMC/B-G
HARTING eCatalogue	https://b2b.harting.com/09628060801

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] EMC/B
	Han [®] High Temp
Type of hood/housing	Hoods
Туре	High construction

Version

Locking type	Single locking lever
Size	6 B
Version	Without cable entry
Field of application	Hoods/Housings for higher EMC requirements

Technical characteristics

Limiting temperature	-40 +125 °C -40 +200 °C With Han® High Temp components
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No



Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	151.5 g
Country of origin	Germany
Customs tariff number	85389099