

Han-Yellock 10 hood M20 top entry



Part number	11 20 003 1400
Specification	Han-Yellock 10 hood M20 top entry
HARTING eCatalogue	https://b2b.harting.com/11200031400

Identification

Category	Hoods/Housings
Series of hoods/housing	[§] Han-Yellock [®]
Type of hood/housing	Hoods

Version

Locking type	Push button
Size	Han-Yellock [®] 10
Version	Top entry
Cable entry	1x M20
Field of application	Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 +125 °C
Un-/locking temperature	-10 +85 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65
	IP67

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7021 (black grey)
Material (locking)	Polyamide Stainless steel
Colour (locking)	Melon yellow
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e



Material properties

REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	189.2 g
Country of origin	Germany
Customs tariff number	85389099