

Han 24B Easy Hood - gs



Part number	11 30 024 0520
Specification	Han 24B Easy Hood - gs
HARTING eCatalogue	https://b2b.harting.com/11300240520

Identification

Category	Hoods/Housings
Series of hoods/housings	Han® Easy Hood
Type of hood/housing	Hoods

Version

Locking type	Double locking lever
Size	24 B
Version	Side entry
Cable entry	1x Integrated

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12
Cable diameter	20 ... 34 mm

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No



Pushing Performance

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	575.8 g
Country of origin	Germany
Customs tariff number	85389099
