

Han Q 8/0 - GS - Metal



Part number	19 12 008 0502
Specification	Han Q 8/0 - GS - Metal
HARTING eCatalogue	https://b2b.harting.com/19120080502

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Compact®
Type of hood/housing	Hoods
Description of hood/housing	for Han-Compact® half cable gland for Han® Q 8/0 Crimp (max. 400 V), Han® Q17/0 and Han® Q Data RJ45

Version

Locking type	Single locking lever
Size	Han-Compact®
Version	Side entry
Cable gland	1x M25
Field of application	Hoods/Housings for higher EMC requirements

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No



Pushing Performance

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	10
Net weight	163.4 g
Country of origin	Germany
Customs tariff number	85389099