

# Han Compact Side Entry Hood M25 HC



Part number	19 12 008 0528
Specification	Han Compact Side Entry Hood M25 HC
HARTING eCatalogue	https://b2b.harting.com/19120080528

### Identification

Category	Hoods/Housings			
Series of hoods/housings Han-Compact®				
Type of hood/housing	Hoods			
	for standard cable gland			
Description of hood/ housing	With separate PE terminating point			
	for all inserts of size Han-Compact®			

#### Version

Locking type	Single locking lever
Size	Han-Compact <sup>®</sup>
Version	Side entry
Cable gland	1x M25
Field of application	Hoods/Housings for higher EMC requirements

# Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65

## Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No



## Specifications and approvals

Approvals	DNV GL	
Commercial data		
Packaging size	1	
Net weight	316.3 g	
Country of origin	Germany	
Customs tariff number	85389099	