

Han 3A-HTE plastic (9-17mm)



| | |
|--------------------|---|
| Part number | 19 20 003 0410 |
| Specification | Han 3A-HTE plastic (9-17mm) |
| HARTING eCatalogue | https://b2b.harting.com/19200030410 |

Identification

| | |
|-----------------------------|-----------------------------|
| Category | Hoods/Housings |
| Series of hoods/housings | Han A® |
| Type of hood/housing | Hoods |
| Description of hood/housing | With integrated cable gland |

Version

| | |
|----------------------|---|
| Locking type | Single locking lever |
| Size | 3 A |
| Version | Top entry |
| Cable entry | 1x Integrated |
| Field of application | Standard Hoods/housings for industrial applications |

Technical characteristics

| | |
|--|---|
| Limiting temperature | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP44 IP67 with seal screw 09 20 000 9918 |
| Type rating acc. to UL 50 / UL 50E | 4 4X 12 |
| Cable diameter | 9 ... 17 mm |

Material properties

| | |
|---|------------------------|
| Material (hood/housing) | Polycarbonate |
| Colour (hood/housing) | RAL 7032 (pebble grey) |
| Material flammability class acc. to UL 94 | V-0 |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | No |



Pushing Performance

Material properties

REACH ANNEX XIV substances No

REACH SVHC substances No

Specifications and approvals

Approvals DNV GL

UL / CSA UL 1977 ECBT2.E235076
CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size 10

Net weight 18.6 g

Country of origin Germany

Customs tariff number 85389099