

3A TE Hood, 9-17 cord grip, glued seal



Part number	19 20 003 0413
Specification	3A TE Hood, 9-17 cord grip, glued seal
HARTING eCatalogue	https://b2b.harting.com/19200030413

Identification

Category	Hoods/Housings
Series of hoods/housings	Han A®
Type of hood/housing	Hoods
Description of hood/housing	With glued seal With integrated cable gland

Version

Locking type	Single locking lever
Size	3 A
Version	Top entry
Cable entry	1x Integrated
Field of application	Standard Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP44 IP67 with seal screw 09 20 000 9918
Type rating acc. to UL 50 / UL 50E	4 4X 12
Cable diameter	9 ... 17 mm

Material properties

Material (hood/housing)	Polycarbonate
Colour (hood/housing)	RAL 7032 (pebble grey)
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance

Material properties

REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	10
Net weight	18.33 g
Country of origin	Germany
Customs tariff number	85389099