

## Han 3A-gw-M20+gekl.Dicht



Part number	19 20 003 0623
Specification	Han 3A-gw-M20+gekl.Dicht
HARTING eCatalogue	<a href="https://b2b.harting.com/19200030623">https://b2b.harting.com/19200030623</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han A®
Type of hood/housing	Hoods
Description of hood/housing	for Han-Brid® With glued seal

### Version

Locking type	Single locking lever
Size	3 A
Version	Side entry
Cable entry	1x M20
Field of application	Standard Hoods/housings for industrial applications

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP44 IP67 with seal screw 09 20 000 9918
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (hood/housing)	Polycarbonate
Colour (hood/housing)	RAL 7032 (pebble grey)
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No



Pushing Performance

## Material properties

REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

## Commercial data

Packaging size	10
Net weight	13.12 g
Country of origin	Romania
Customs tariff number	85389099