

# Han 3A Hood Top Entry M25 Low Constr.



Part number	19 20 003 1421
Specification	Han 3A Hood Top Entry M25 Low Constr.
HARTING eCatalogue	https://b2b.harting.com/19200031421

## Identification

Category	Hoods/Housings	
Series of hoods/housings Han A®		
Type of hood/housing	Hoods	
Description of hood/ housing	With integrated cable gland	

#### Version

Locking type	Single locking lever
Size	3 A
Version	Top entry
Cable entry	1x Integrated
Field of application	Standard Hoods/housings for industrial applications

#### Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP44 IP65 / IP67 with seal screw 09 20 000 9918
Cable diameter	6 12 mm

## Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



# Material properties

REACH SVHC substances Yes

REACH SVHC substances Lead

# Specifications and approvals

Approvals DNV GL

#### Commercial data

Packaging size	10
Net weight	78.8 g
Country of origin	Germany
Customs tariff number	85389099