

## Han 6B-HSE-CL-M32



Part number	19 30 006 0587
Specification	Han 6B-HSE-CL-M32
HARTING eCatalogue	<a href="https://b2b.harting.com/19300060587">https://b2b.harting.com/19300060587</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> B
Type of hood/housing	Hoods
Type	High construction

### Version

Locking type	Central locking lever (on the hood)
Size	6 B
Version	Side entry
Cable entry	1x M32
Field of application	Standard hoods/housings for industrial connectors

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

## Material properties

REACH SVHC substances	No
-----------------------	----

---

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	1
Net weight	281.6 g
Country of origin	Germany
Customs tariff number	85389099

---