

## Han B HOOD SIDE ENTRY LC 2 PEGS M25



Part number	19 30 006 1541
Specification	Han B HOOD SIDE ENTRY LC 2 PEGS M25
HARTING eCatalogue	<a href="https://b2b.harting.com/19300061541">https://b2b.harting.com/19300061541</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> B
Type of hood/housing	Hoods
Type	Low construction

### Version

Locking type	Single locking lever
Size	6 B
Version	Side entry
Cable entry	1x M25
Field of application	Standard hoods/housings for industrial connectors

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65 IP67 in combination with special bulkhead mounted housings
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

## Material properties

REACH SVHC substances	No
-----------------------	----

## Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

## Commercial data

Packaging size	1
Net weight	99.6 g
Country of origin	Germany
Customs tariff number	85389099