

Han 16B-gs-M40



Part number	19 30 016 0523	
Specification	Han 16B-gs-M40	
HARTING eCatalogue	https://b2b.harting.com/19300160523	
Identification		
Category	Hoods/Housings	
Series of hoods/housings Han [®] B		
Type of hood/housing	Hoods	
Description of hood/ housing	Special type	
Туре	High construction	

Version

Locking type	Double locking lever
Size	16 B
Version	Side entry
Cable entry	1x M40
Field of application	Standard hoods/housings for industrial connectors

Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65 IP67 in combination with special bulkhead mounted housings
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No

Page 1 / 2 | Creation date 2018-09-07 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric GmbH & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com Product data sheet 19 30 016 0523 Han 16B-gs-M40



Material properties

REACH ANNEX XIV substances	No
REACH SVHC substances	No
Specifications and approvals	
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Commercial data	
Packaging size	1
Net weight	351.8 g
Country of origin	China
Customs tariff number	8538900000