

Han B Hood Top Entry HC M32



Part number	19 30 024 0467	
Specification	Han B Hood Top Entry HC M32	
HARTING eCatalogue	https://b2b.harting.com/19300240467	
Identification		
Category	Hoods/Housings	
Series of hoods/housings Han [®] B		
Type of hood/housing	Hoods	
Туре	High construction	

Version

Locking type	Double locking lever
Size	24 B
Version	Top entry
Cable entry	2x M32
Field of application	Standard hoods/housings for industrial connectors
Technical characteristics	
Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65 IP67 in combination with special bulkhead mounted housings
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material (hood/housing) Aluminium die-cast Surface (hood/housing) Powder-coated Colour (hood/housing) RAL 7037 (dust grey) RoHS compliant ELV status compliant China RoHS е **REACH Annex XVII substances** No **REACH ANNEX XIV substances** No

Page 1 / 2 | Creation date 2018-09-07 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric GmbH & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



Material properties	
REACH SVHC substances	No
Specifications and approvals	
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076
Commercial data	
Packaging size	1
Net weight	256.1 g
Country of origin	Germany
Customs tariff number	85389099