

Han 24B side entry hood HC M50 (30°)



Part number	19 30 024 0529
Specification	Han 24B side entry hood HC M50 (30°)
HARTING eCatalogue	https://b2b.harting.com/19300240529

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] B
Type of hood/housing	Hoods
Description of hood/housing	Special type
Type	High construction

Version

Locking type	Double locking lever
Size	24 B
Version	Side entry
Cable entry	1x M50
Field of application	Standard hoods/housings for industrial connectors

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65 IP67 in combination with special bulkhead mounted housings
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No



Pushing Performance

Material properties

REACH ANNEX XIV substances No

REACH SVHC substances No

Specifications and approvals

Approvals DNV GL

UL / CSA UL 1977 ECBT2.E235076
CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size 1

Net weight 356 g

Country of origin Germany

Customs tariff number 85389099