

Han B Hood Side Entry HC 2 Levers M32



0 024 0537
B Hood Side Entry HC 2 Levers
://b2b.harting.com/19300240537

Identification

Category	Hoods/Housings	
Series of hoods/housings Han® B		
Type of hood/housing	Hoods	
Туре	High construction	

Version

Locking type	Double locking lever (on the hood)
Han-Easy Lock [®]	Yes
Size	24 B
Version	Side entry
Cable entry	1x M32
Field of application	Standard hoods/housings for industrial connectors

Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (locking)	Polycarbonate Stainless steel
Colour (locking)	RAL 7037 (dust grey)
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant



Material properties

ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL	
-----------	--------	--

Commercial data

Packaging size	1
Net weight	304.6 g
Country of origin	Germany
Customs tariff number	85389099