

Han 3M Hood Top Entry M20 glued seal



Part number	19 37 003 1443
Specification	Han 3M Hood Top Entry M20 glued seal
HARTING eCatalogue	https://b2b.harting.com/19370031443

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] M
Type of hood/housing	Hoods
Description of hood/housing	With glued seal

Version

Locking type	Single locking lever
Size	3 A
Version	Top entry
Cable gland	1x M20
Field of application	Hoods/housings for rough environments

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP44 IP65 / IP67 with seal screw 09 20 000 9918

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	FPM
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No



Pushing Performance

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	10
Net weight	63.3 g
Country of origin	Germany
Customs tariff number	85389099