

Han 24M-gs-ZV-M32



Part number	19 37 024 0587
Specification	Han 24M-gs-ZV-M32
HARTING eCatalogue	https://b2b.harting.com/19370240587

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] M
Type of hood/housing	Hoods
Type	High construction

Version

Locking type	Central locking lever (on the hood)
Size	24 B
Version	Side entry
Cable gland	1x M32
Field of application	Hoods/housings for rough environments

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	FPM
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No



Pushing Performance

Material properties

REACH ANNEX XIV substances No

REACH SVHC substances No

Specifications and approvals

Approvals DNV GL

UL / CSA
UL 1977 ECBT2.E235076
CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size 1

Net weight 459.8 g

Country of origin Germany

Customs tariff number 85389099