

Han 24M-gg-M25



Part number	19 37 024 1421
Specification	Han 24M-gg-M25
HARTING eCatalogue	https://b2b.harting.com/19370241421

Identification

Category	Hoods/Housings
Series of hoods/housings Han® M	
Type of hood/housing	Hoods
Туре	Low construction

Version

Locking type	Double locking lever
Size	24 B
Version	Top entry
Cable gland	1x M25
Field of application	Hoods/housings for rough environments

Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Material properties

|--|

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	220.5 g
Country of origin	Germany
Customs tariff number	85389099