

# Han 10HPR-gg-SV-M25



Part number	19 40 010 0411
Specification	Han 10HPR-gg-SV-M25
HARTING eCatalogue	https://b2b.harting.com/19400100411

### Identification

Category	Hoods/Housings
Series of hoods/housingsHan® HPR	
Type of hood/housing	Hoods

#### Version

Locking type	Screw locking
Size	10 B
Version	Top entry
Cable gland	1x M25
Field of application	Hoods/housings for harsh outdoor environments

#### Technical characteristics

Limiting temperature	-40 +125 °C
Tightening torque (screw locking)	4 Nm
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4 4X 12

# Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No



## Material properties

REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

### Commercial data

Packaging size	1
Net weight	496.2 g
Country of origin	Germany
Customs tariff number	85389099