

Han 24HPR Hood Top Entry 2xM40 Screw loc



Part number	19 40 024 0438
Specification	Han 24HPR Hood Top Entry 2xM40 Screw loc
HARTING eCatalogue	https://b2b.harting.com/19400240438

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] HPR
Type of hood/housing	Hoods
Description of hood/housing	With adapter

Version

Locking type	Screw locking
Size	24 B
Version	Top entry
Cable gland	2x M40
Field of application	Hoods/housings for harsh outdoor environments

Technical characteristics

Limiting temperature	-40 ... +125 °C
Tightening torque (screw locking)	4 Nm
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (locking)	Stainless steel
RoHS	compliant with exemption



Pushing Performance

Material properties

RoHS exemptions 6c: Copper alloy containing up to 4 % lead by weight

ELV status compliant with exemption

China RoHS 50

REACH Annex XVII substances No

REACH ANNEX XIV substances No

REACH SVHC substances Yes

REACH SVHC substances Lead

Specifications and approvals

Approvals DNV GL

UL / CSA UL 1977 ECBT2.E235076
CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size 1

Net weight 920.5 g

Country of origin Germany

Customs tariff number 85389099