

# Han-Eco Mod.10-HTE-M32



Part number	19 41 010 0422
Specification	Han-Eco Mod.10-HTE-M32
HARTING eCatalogue	https://b2b.harting.com/19410100422

### Identification

Category	Hoods/Housings	
Series of hoods/housings Han-Eco® Modular		
Type of hood/housing	Hoods	

#### Version

Locking type	Double locking lever
Size	10 B
Version	Top entry
Cable entry	1x M32

### Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65

## Material properties

Material (hood/housing)	Polyamide Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

# Specifications and approvals

	IEC 61984
Specifications	EN 45545-2 R22: HL1, HL2, HL3
	EN 45545-2 R23: HL1, HL2, HL3



## Specifications and approvals

	EN 45545-2 R24: HL1, HL2, HL3
UL / CSA	UL 1977 ECBT2.E235076
UL / CSA	CSA-C22.2 No. 182.3 ECBT8.E235076

#### Commercial data

Packaging size	1
Net weight	119.4 g
Country of origin	Germany
Customs tariff number	85389099