

## Han-Eco Mod.24-HSE-M40



Part number	19 41 024 0523
Specification	Han-Eco Mod.24-HSE-M40
HARTING eCatalogue	<a href="https://b2b.harting.com/19410240523">https://b2b.harting.com/19410240523</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Eco® Modular
Type of hood/housing	Hoods

### Version

Locking type	Double locking lever
Size	24 B
Version	Side entry
Cable entry	1x M40

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65

### Material properties

Material (hood/housing)	Polyamide Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

### Specifications and approvals

Specifications	IEC 61984 EN 45545-2 R22: HL1, HL2, HL3 EN 45545-2 R23: HL1, HL2, HL3
----------------	---



Pushing Performance

## Specifications and approvals

	EN 45545-2 R24: HL1, HL2, HL3
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

## Commercial data

Packaging size	1
Net weight	211.8 g
Country of origin	Germany
Customs tariff number	85389099