

Han 3EMC-HTE-2 Pegs-M20



Part number	19 62 003 1440
Specification	Han 3EMC-HTE-2 Pegs-M20
HARTING eCatalogue	https://b2b.harting.com/19620031440

Identification

Category	Hoods/Housings	
Series of hoods/housings Han® EMC		
Type of hood/housing	Hoods	

Version

Locking type	Single locking lever
Size	3 A
Version	Top entry
Cable gland	1x M20
Field of application	Hoods/Housings for higher EMC requirements

Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP44
	IP65 / IP67 with seal screw 09 20 000 9918

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No



Specifications and approvals

Approvals	DNV GL	
Commercial data		
Packaging size	10	
Net weight	61.7 g	
Country of origin	Germany	
Customs tariff number	85389099	