

## Han 3 EMC HOOD ANGLED ENTRY 2PEGS M20



|                    |   |
|--------------------|---|
| Part number        | 19 62 003 1640  |
| Specification      | Han 3 EMC HOOD ANGLED ENTRY 2PEGS M20   |
| HARTING eCatalogue | <a href="https://b2b.harting.com/19620031640">https://b2b.harting.com/19620031640</a> |

### Identification

|                          |                      |
|--------------------------|----------------------|
| Category                 | Hoods/Housings       |
| Series of hoods/housings | Han <sup>®</sup> EMC |
| Type of hood/housing     | Hoods                |

### Version

|                      |  |
|----------------------|--|
| Locking type         | Single locking lever                       |
| Size                 | 3 A  |
| Version              | Side entry                                 |
| Cable gland          | 1x M20                                     |
| Field of application | Hoods/Housings for higher EMC requirements |

### Technical characteristics

|  |  |
|--|--|
| Limiting temperature                   | -40 ... +125 °C                                    |
| Degree of protection acc. to IEC 60529 | IP44<br>IP65 / IP67 with seal screw 09 20 000 9918 |

### Material properties

|                             |               |
|-----------------------------|---------------|
| Material (hood/housing)     | Zinc die-cast |
| Surface (hood/housing)      | Uncoated      |
| Colour (hood/housing)       | Unpainted     |
| RoHS                        | compliant     |
| ELV status                  | compliant     |
| China RoHS                  | e             |
| REACH Annex XVII substances | No            |
| REACH ANNEX XIV substances  | No            |
| REACH SVHC substances       | No            |



Pushing Performance

## Specifications and approvals

|           |        |
|-----------|--------|
| Approvals | DNV GL |
|-----------|--------|

## Commercial data

|                       |          |
|-----------------------|----------|
| Packaging size        | 10       |
| Net weight            | 80.7 g   |
| Country of origin     | Germany  |
| Customs tariff number | 85389099 |