

## Han EMC 25 Hood Top Entry M25



Part number	19 62 025 0446
Specification	Han EMC 25 Hood Top Entry M25
HARTING eCatalogue	<a href="https://b2b.harting.com/19620250446">https://b2b.harting.com/19620250446</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> EMC
Type of hood/housing	Hoods

### Version

Locking type	Single locking lever
Size	16 A
Version	Top entry
Cable entry	1x M25
Field of application	Hoods/Housings for higher EMC requirements

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 12

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No



Pushing Performance

## Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

## Commercial data

Packaging size	1
Net weight	159.5 g
Country of origin	Germany
Customs tariff number	85389099