

Han EMC 25 Hood Side Entry M25



| | |
|--------------------|---|
| Part number | 19 62 025 0546 |
| Specification | Han EMC 25 Hood Side Entry M25 |
| HARTING eCatalogue | https://b2b.harting.com/19620250546 |

Identification

| | |
|--------------------------|----------------------|
| Category | Hoods/Housings |
| Series of hoods/housings | Han [®] EMC |
| Type of hood/housing | Hoods |

Version

| | |
|----------------------|--|
| Locking type | Single locking lever |
| Size | 16 A |
| Version | Side entry |
| Cable entry | 1x M25 |
| Field of application | Hoods/Housings for higher EMC requirements |

Technical characteristics

| | |
|--|-----------------|
| Limiting temperature | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP65 |
| Type rating acc. to UL 50 / UL 50E | 4 12 |

Material properties

| | |
|-----------------------------|--------------------|
| Material (hood/housing) | Aluminium die-cast |
| Surface (hood/housing) | Uncoated |
| Colour (hood/housing) | Unpainted |
| Material (seal) | NBR |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | No |



Pushing Performance

Specifications and approvals

| | |
|-----------|--|
| Approvals | DNV GL |
| UL / CSA | UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076 |

Commercial data

| | |
|-----------------------|----------|
| Packaging size | 1 |
| Net weight | 162.2 g |
| Country of origin | Germany |
| Customs tariff number | 85389099 |