

## Han EMC Hood Side Entry M40



|                    |   |
|--------------------|---|
| Part number        | 19 62 064 0543  |
| Specification      | Han EMC Hood Side Entry M40   |
| HARTING eCatalogue | <a href="https://b2b.harting.com/19620640543">https://b2b.harting.com/19620640543</a> |

### Identification

|                          |                      |
|--------------------------|----------------------|
| Category                 | Hoods/Housings       |
| Series of hoods/housings | Han <sup>®</sup> EMC |
| Type of hood/housing     | Hoods                |

### Version

|                      |  |
|----------------------|--|
| Locking type         | Screw locking                              |
| Size                 | 24 B                                       |
| Version              | Side entry                                 |
| Cable entry          | 1x M40                                     |
| Field of application | Hoods/Housings for higher EMC requirements |

### Technical characteristics

|  |                 |
|--|-----------------|
| Limiting temperature                   | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP65            |
| Type rating acc. to UL 50 / UL 50E     | 4<br>12         |

### Material properties

|                             |                    |
|-----------------------------|--------------------|
| Material (hood/housing)     | Aluminium die-cast |
| Surface (hood/housing)      | Uncoated           |
| Colour (hood/housing)       | Unpainted          |
| RoHS                        | compliant          |
| ELV status                  | compliant          |
| China RoHS                  | e                  |
| REACH Annex XVII substances | No                 |
| REACH ANNEX XIV substances  | No                 |
| REACH SVHC substances       | No                 |



Pushing Performance

## Specifications and approvals

|           |  |
|-----------|--|
| Approvals | DNV GL   |
| UL / CSA  | UL 1977 ECBT2.E235076<br>CSA-C22.2 No. 182.3 ECBT8.E235076 |

## Commercial data

|                       |          |
|-----------------------|----------|
| Packaging size        | 1        |
| Net weight            | 390 g    |
| Country of origin     | Germany  |
| Customs tariff number | 85389099 |