

Han 6EMC/B-HTE-M20 (HT)



| | |
|--------------------|---|
| Part number | 19 62 806 1440 |
| Specification | Han 6EMC/B-HTE-M20 (HT) |
| HARTING eCatalogue | https://b2b.harting.com/19628061440 |

Identification

| | |
|--------------------------|------------------------------|
| Category | Hoods/Housings |
| Series of hoods/housings | Han® EMC/B Han® High Temp |
| Type of hood/housing | Hoods |
| Type | Low construction |

Version

| | |
|--------------|----------------------|
| Locking type | Single locking lever |
| Size | 6 B |
| Version | Top entry |
| Cable entry | 1x M20 |

Technical characteristics

| | |
|--|---|
| Limiting temperature | -40 ... +125 °C -40 ... +200 °C With Han® High Temp components |
| Degree of protection acc. to IEC 60529 | IP65 |
| Type rating acc. to UL 50 / UL 50E | 4 12 |

Material properties

| | |
|-----------------------------|--------------------|
| Material (hood/housing) | Aluminium die-cast |
| Surface (hood/housing) | Uncoated |
| Colour (hood/housing) | Unpainted |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | No |



Pushing Performance

Specifications and approvals

| | |
|-----------|--|
| Approvals | DNV GL |
| UL / CSA | UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076 |

Commercial data

| | |
|-----------------------|----------|
| Packaging size | 1 |
| Net weight | 103.4 g |
| Country of origin | Germany |
| Customs tariff number | 85389099 |