

## Han 10EMC/B-HTE-M32 (HT)



|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| Part number        | 19 62 810 0427                                                                        |
| Specification      | Han 10EMC/B-HTE-M32 (HT)                                                              |
| HARTING eCatalogue | <a href="https://b2b.harting.com/19628100427">https://b2b.harting.com/19628100427</a> |

### Identification

|                          |                              |
|--------------------------|------------------------------|
| Category                 | Hoods/Housings               |
| Series of hoods/housings | Han® EMC/B<br>Han® High Temp |
| Type of hood/housing     | Hoods                        |
| Type                     | High construction            |

### Version

|              |                      |
|--------------|----------------------|
| Locking type | Double locking lever |
| Size         | 10 B                 |
| Version      | Top entry            |
| Cable entry  | 1x M32               |

### Technical characteristics

|                                        |                                                                   |
|----------------------------------------|-------------------------------------------------------------------|
| Limiting temperature                   | -40 ... +125 °C<br>-40 ... +200 °C With Han® High Temp components |
| Degree of protection acc. to IEC 60529 | IP65                                                              |
| Type rating acc. to UL 50 / UL 50E     | 4<br>12                                                           |

### Material properties

|                             |                    |
|-----------------------------|--------------------|
| Material (hood/housing)     | Aluminium die-cast |
| Surface (hood/housing)      | Uncoated           |
| Colour (hood/housing)       | Unpainted          |
| RoHS                        | compliant          |
| ELV status                  | compliant          |
| China RoHS                  | e                  |
| REACH Annex XVII substances | No                 |
| REACH ANNEX XIV substances  | No                 |
| REACH SVHC substances       | No                 |



Pushing Performance

## Specifications and approvals

|           |                                                            |
|-----------|------------------------------------------------------------|
| Approvals | DNV GL                                                     |
| UL / CSA  | UL 1977 ECBT2.E235076<br>CSA-C22.2 No. 182.3 ECBT8.E235076 |

## Commercial data

|                       |          |
|-----------------------|----------|
| Packaging size        | 1        |
| Net weight            | 160.3 g  |
| Country of origin     | Germany  |
| Customs tariff number | 85389099 |