

Han 16EMC/B-HTE-M32 (HT)



Part number	19 62 816 0427
Specification	Han 16EMC/B-HTE-M32 (HT)
HARTING eCatalogue	https://b2b.harting.com/19628160427

Identification

Category	Hoods/Housings
Series of hoods/housings	Han® EMC/B Han® High Temp
Type of hood/housing	Hoods
Type	High construction

Version

Locking type	Double locking lever
Size	16 B
Version	Top entry
Cable entry	1x M32

Technical characteristics

Limiting temperature	-40 ... +125 °C -40 ... +200 °C With Han® High Temp components
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No



Pushing Performance

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	217.7 g
Country of origin	Germany
Customs tariff number	85389099