

## Han Split Hood 16 B



Part number	09 30 016 0408
Specification	Han Split Hood 16 B
HARTING eCatalogue	<a href="https://b2b.harting.com/09300160408">https://b2b.harting.com/09300160408</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> B
Type of hood/housing	Panel feed through housing

### Version

Locking type	Double locking lever
Size	16 B
Version	Top entry
Cable entry	3x Integrated
Field of application	Standard hoods/housings for industrial connectors
Details	Please order cable entry seals separately.
Pack contents	2 split hood halves

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP54 when mounted vertically IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12
Cable diameter	17.6 mm

### Material properties

Material (hood/housing)	Polycarbonate
Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

## Material properties

REACH SVHC substances No

---

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
----------	--

---

## Commercial data

Packaging size	1
Net weight	44 g
Country of origin	Germany
Customs tariff number	85389099

---