

## Han 3A Bulkhead feed-thru housing



Part number	19 20 003 1120
Specification	Han 3A Bulkhead feed-thru housing
HARTING eCatalogue	<a href="https://b2b.harting.com/19200031120">https://b2b.harting.com/19200031120</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han A®
Type of hood/housing	Panel feed through housing

### Version

Locking type	Single locking lever
Size	3 A
Version	Top entry
Cable gland	1x M20
Field of application	Standard Hoods/housings for industrial applications

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP44 IP65 / IP67 with seal screw 09 20 000 9918

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
Material (locking)	Steel
Surface (locking)	Zinc plated
RoHS	compliant with exemption
RoHS exemptions	6a: Lead as an alloying element in steel for machining purposes and in galvanised steel containing up to 0,35 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

## Material properties

REACH SVHC substances	Yes
REACH SVHC substances	Lead

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	10
Net weight	100.06 g
Country of origin	Germany
Customs tariff number	85389099