

# Han 6HPR-PFT housing-M40



Part number	19 40 006 1113	
Specification	Han 6HPR-PFT housing-M40	
HARTING eCatalogue	https://b2b.harting.com/19400061113	
Identification		
Category	Hoods/Housings	
Series of hoods/housings Han <sup>®</sup> HPR		
Type of hood/housing	Panel feed through housing	
Description of hood/ housing	for mounting from inside	

#### Version

Material (seal)

Locking type	Screw locking
Size	6 B
Version	Top entry
Cable entry	1x M40
Field of application	Hoods/housings for harsh outdoor environments
Technical characteristics	
Limiting temperature	-40 +125 °C
Tightening torque (screw locking)	4 Nm
Tightening torque	6 Nm Fixing screws
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4 4X 12
Thickness of the panel	≥2 mm
Material properties	
Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)

Page 1 / 2 | Creation date 2018-09-04 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric GmbH & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

NBR



#### Material properties

Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

### Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

## Commercial data

Packaging size	1
Net weight	987.5 g
Country of origin	China
Customs tariff number	8538900000